

NSG 432 Electrostatic Discharge Simulator





Electrostatic charges

Electrostatic charges are an everyday phenomenon. Materials that have differing dielectric constants become mutually charged through friction and can sometimes achieve quite significant voltages. The most well-known example is the charge generated by people walking on an insulated floor covering with the subsequent discharge through a spark when approaching a conductive article. Although unpleasant for the person involved, it is in fact harmless. Not so for electronic circuitry where the occurrence can have deadly effects. The high discharge current that

results, and the consequent high electromagnetic field that is induced, can lead to faulty operation in office automation systems, computer installations, industrial electronic plant, automotive electronics, etc. (program errors, data loss, wild control signals) or to destruction of hardware components. Only systematic testing with simulation generators can ensure that items of equipment can withstand such disruptive effects in practice and that no damage with associated economic penalties results.



NSG 432 Static Discharge Simulator

The Simulator type NSG 432 generates static discharges of up to 25 kV in a defined and reproducible form. The handy shape, user-friendly controls and a range of accessories make the NSG432 into a highly practical and universal ESD test instrument. The instrument is modularly built. Various discharge networks can be attached to the generator section thereby making the unit suitable for carrying out tests

according to various standards. A range of power supply units, including a mains-independent battery-pack, cover numerous user needs. A relay adapter enables testing to be carried out in conformity with the latest IEC recommendations. A wealth of accessories such as E-field/H-field adapters, measuring targets, etc. complete the range of possibilities offered by this flexible simulator.





Technical specifications

(in conformity with IEC 801-2)

Discharge voltage V.

(air-discharge) 2 - 25 kV

(0.2 - 2.5 kV optional)

Discharge voltage V, (with contact discharge

2 - 9 kV adapter)

Polarity Discharge capacitor C. Discharge resistor R,

positive/negative 150 pF ± 10 % $330 \Omega \pm 10 \%$

or other value, depending on the discharge network

Operating modes single/repetitive discharge

conforms to IEC 801-2 Test finger

Max. discharge energy 350 mJ

(47 mJ at 150 pF)

Rise time (air-discharge) Rise time

< 1 ns for voltages ≤ 8 kV

(with contact discharge

0.7 - 1 ns adapter) First current peak (with

contact discharge adapter) at a voltage

2 kV set to: 15 A ± 10 % 4 kV 6 kV

> 8 kV 30 A ± 10 %


Current pulse shape

Voltage indication tolerance (LCD) ±5% Holding time >58 Charging resistor R_{ch} 100 MΩ

7.5 A ± 10 %

22.5 A ± 10 %

conforms to IEC 801-2



generator to its power supply. A tripod mount is

provided for testing that requires a large number of



- IEC 801-2 Electrostatic discharge Requirements
- EN 55101-2 ESD Requirements
- ISO/CD 10605/E Road Vehicles - Electrical Disturbance from Electrostatic Discharges
- SAE J1113, Part 5 Susceptibility to Electrostatic Discharges
- ANSI IEEE Guide for electrostatic discharge test methodologies and criteria for electronic equipment
- VDE 0847, Part 2 Measurement techniques for the assessment of electromagnetic compatibility (Messverfahren zur Beurteilung der elektromagnetischen Verträglichkeit)
- ECMA

discharges.

- European computer manufacturers association
- ESD immunity testing of ITE, TR/40
- MIL-STD-883C Electrostatic Discharge Sensitivity Classification
- etc.





NSG 432 Base set



The base set includes:

- Carrying case in which accommodation is provided for the additional items
- · Standard-conforming ground cable
- · Spacers to set fixed distances between the test finger and EUT
- IEC discharge sphere
- · Operating instructions

Power supplies

Three different power supplies are available to suit differing requirements.



Mains unit

A simple power supply with fuse and IEC cable; mains input voltage and connector as per order page.



Mains unit with preset counter

In this case, a counter is incorporated for presetting a defined number of discharges by means of an internal 1 Hz generator or with external triggering. The presettable counter is particularly useful in combination with the contact discharge adapter.



Battery-pack

A rechargeable battery supply that makes the generator mains-independent with consequently greater freedom of use. Storage capacity is sufficient for up to 10 hours of testing. Charging unit for 110 Vac or 220 Vac as per order page.







Discharge networks



The required high voltage is produced in these modules through cascading. They also contain the various standard-conforming discharge networks.



Simple equivalent circuit



Typical discharge pulse for a discharge through air

Standard 25 kV discharge networks

Modules, that are standard products, with RC values corresponding to the most common Standards:.

- + 150 pF/150 Ω
- 150 pF/150 Ω (IEC 801-2,1984)
- + 150 pF/330 Ω
- 150 pF/330 Ω (IEC 801-2.1990)
- + 150 pF/2 kΩ
- 150 pF/2 kΩ (SAE J1113; ISO)

- + 330 pF/2 kΩ
- 330 pF/2 kΩ (SAE J1113; ISO)

Special 25 kV discharge networks

Modules produced to order with RC values and polarity specified by the customer (Cmax = 1200pF).

Special 2.5 kV discharge networks

Special versions for applications at the IC and PCB level.

Voltage range: 200 V ... 2.5 kV

The RC values and polarity have to be specified.

E- and H- field adapter set

(supplied as a set)



H-field adapter

Current-loop to check the interference immunity of circuit boards and equipment against electromagnetically induced disturbances.



E-field adapter and coupling piece

The disc-electrode produces a homogeneous Efield. Field breakdown upon arcing results in a very fast pulse rise time.



Adiustable discharge gap

A spark-gap that can be calibrated for the H-field adapter and a simple substitute for direct contact tests.

Measuring targets



Target (402-283) for IEC 801-2 (1984)



Target MD 101 for IEC 801-2 (1990) Coaxial measurement attenuator as specified by IEC 801-2 (1990) for mounting in the Faradaycage of a screened oscilloscope.




Contact discharge adapter (Add-on HV relay)




The reproducibility of conventional discharge tests is affected to some extent by environmental influences (air pressure, humidity and temperature). Predischarges, which depend on the speed of approach and the shape of the electrode, also affect the pulse form as well as the arcing voltage during tests.

In order to improve the reproducibility, the new Standards (e.g.IEC 801-2, 1990, ANSI-IEEE, ECMA) specify ESD simulation using the direct contact method. The CONTACT DISCHARGE ADAPTER meets these recommendations and enables precisely reproducible electrostatic discharge tests to be carried out irrespective of external influences. The device produces specification-true fast discharge pulses with rise times of < 1 ns. The adapter is simply mounted on the test finger of the generator.

The CONTACT DISCHARGE ADAPTER is available in two versions with Rv = 0 Ω or Rv = 180 Ω . The version has to be chosen such that a total resistance of 330 Ω results when added to the Rd of the discharge network.



Principle of operation



Typical pulse shape: first current peak

Technical specifications

Charging voltage

2 ... 9 kV,

Orial girly voltage

approx. 10 kV max.

Rise time tr

0.7 ... 1 ns

Polarity

positive or negative (depending on the cascade)

Triggering: NSG 432

- Manually

with preset counter version of the mains unit:

- 1 Hz automatically

- external trigger

Current peak values

IEC-Level	Open circuit output voltage	Current value		
1	2 kV	7.5 A		
2	4 kV	15 A		
3	6 kV	22.5 A		
4	8 kV	30 A		

Mechanical specifications

Dimensions approx.

80 x 80 x 60 mm

(3.15" x 3.15" x 3.35")

Weight approx.

0.350 kg (0.77 lbs)





NSG 432 Order List

A copy of this page can serve as an order form directly when completed with the quantity (Qty) required.

BASIC EQUIPMENT

Minimum requirement: 1 Base set, 1 Power supply, 1 Discharge network

BASE SET		POWER SUPPLY UNITS			DISCHARGE NETWORKS				
Set consisting of: Ord.No. Oty.		Mains unit without preset counter inkl, mains cable and fuse			Standard 25 kV discharge networks				
	125	Connector type	Ord.No.	Qty.	Vers	ion		Ord.No.	Qty.
Carrying case Basic unit Bracket Earthing cable Spacing adapter Discharge sphere Manual English Manual French Manual German		Swiss Type 13,(02) 402-9 USA, UL 498/13,(04) 402-9 GB, BS 1363,(05) 402-9 Mains unit with preset cour inkl. mains cable and fuse Connector type Ord. N Schuko,(11) 402-9 USA, UL 498/13,(14) 402-9 USA, UL 498/13,(14) 402-9			+ 150 pF 330Ω				
		Rechargeable battery-pack incl. charging unit			Special 2.5 kV discharge networks Special version Qty				
		Version	Ord.No.	Qty.	+	pF	Ω		
		Battery-pack incl. 220Vac charger Battery-pack incl. 110Vac charger	402-915 402-916	ure	me	nt ir	nstri		its

			OPT	IONS				
CONTACT-DISCHARGE ADAPTER		E- and H- FIELD ADAPTER SET			MEASURING TARGETS			
Contact-Discharge $R_v = 0 \Omega$ incl. connecting care $R_v = 180 \Omega$ incl. connecting care $R_v = 180 \Omega$ incl. connecting care	Ord.No. 402-664 ble e Adapter Ord.No. 402-619	Oty.	Adapter Set Set consisting of: H-field adapter E-field adapter Discharge sphere Coupling piece adjustable spark-		Qty.	Measuring target IEC 801-2 (1984) Measuring target IEC 801-2 (1990)	Ord.No. 402-283 Ord.No. MD 101	Oty.

Pate:	Sender:	Signature: